

MPT-141-9T

High Field Hall Effect Probe

High Field Application (up to 9 Tesla)

High Accuracy: $\pm 0.05\%$ max. error at 25°C above 2.2T*
 Calibration tables at 0, 25 and 50°C supplied

* Contribution of probe only. This probe is intended for high field measurements above 2.2T up to its maximum calibrated field point. Use a standard MPT-141 probe if measuring fields below 2.2T.



Specifications

The MPT-141-9T High Field Hall Effect Probe is most suitable to be use with a DTM-151 or DTM-152 Digital Teslameter. Probe can be calibrated to measure field up to 9 Tesla. Transverse orientation reads (+) when field vector enters the top epoxy surface.

Accuracy at 25°C:

$\pm 0.05\%$ of reading + 0.006% of full scale above 2.2T at 25°C

Operating Range:

- 4- Range Operation.
- 1.2, 3.0, 6.0, 9.0 Tesla Full Scale
- 12, 30, 60, 90 Kilo Gauss Full Scale

NOTE: Ranges 3.0 and 6.0 could only display calibrated readings up to 2.2T. Reading above 2.2T on those ranges are not calibrated and it is highly recommended to use Range 9.0 for measurements above 2.2T.

Temperature Stability:


- Calibration: ± 10 ppm of reading/°C max.
- 3ppm/°C of reading per meter of probe cable
- Zero Drift: $\pm (1\mu T + 0.0003\%$ of full scale)/°C max.

Temperature Range:

0 to 50°C operating to spec, -20 to +60°C max.

Dimensions:

- Probe Head Size: 14 x 5 x 2 mm
- Sensitive Area: 1 x 0.5 mm
- Unshielded part of cable at probe head: 5.0 \pm 0.2mm, 300 mm nominal length
- Shielded Cable: \varnothing 7.2 \pm 0.2 mm



ORDER CODE:

MPT-141-9T-7S for probe with basic 7 meters shielded cable.
 Special probe cable lengths may be ordered up to 30 meters.

Probe Accessories:

- MPT Transverse Probe Holder – Part No. 17000081
- MPT Axial Probe Holder – Part No. 17000100

Resolution using DTM-151 Digital Teslameter:

TABLE 1 - DC Mode with Digital Filtering ON
 1 in 600,000 of bipolar scan in front of panel display

Range	Display resolution		Serial / GPIB Output Resolution	
	Gauss	Tesla	Gauss	Tesla
1.2	0.1	0.00001	0.01	0.000001
3.0	0.01	0.000001	0.01	0.000001
6.0	0.2	0.00002	0.1	0.00001
9.0	1	0.0001	0.1	0.00001

TABLE 2 - DC Mode with Digital Filtering OFF, and AC Mode,
 1 in 120,000 of bipolar scan in front of panel display

Range	Display resolution		Serial / GPIB Output Resolution	
	Gauss	Tesla	Gauss	Tesla
1.2	0.2	0.00002	0.01	0.000001
3.0	0.5	0.00005	0.01	0.000001
6.0	1	0.0001	0.1	0.00001
9.0	2	0.0002	0.1	0.00001